

## PRODUCT DATASHEET

### QT-FIT8 1X18

QUICKTRONIC® FIT 8 | ECG for FL 26 mm



#### Areas of application

- Open-plan offices, corridors and storage rooms
- Public buildings
- Strip lighting
- Suitable for emergency lighting (DC operation)
- Suitable for luminaires of protection class I

#### Product benefits

- Long lamp life
- No adverse effect from frequent on/off switching
- Automatic restart after lamp replacement
- Perfect lamp start for applications with motion sensors
- VDE/VDE EMC certified system
- Very high energy efficiency due to cut-off technology

#### Product features

- Supply voltage: 220...240 V
- Line voltage: 198...264 V
- Line frequency: 50 Hz | 60 Hz
- Lamp start with optimum filament preheating

- Energy Efficiency Index EEI: A2
- Automatic shutdown of defective lamps and at end of life (EoL T.2)
- Lamp operation: to EN 60929
- Safety: to EN 61347-2-3

## TECHNICAL DATA

### Electrical data

Nominal wattage	18.00 W
Nominal voltage	220...240 V
Input voltage AC	198...264 V
Input voltage DC	185...264 V <sup>1)</sup>
U-OUT (working voltage)	430 V
Inrush current	15 A
Mains frequency	50/60 Hz
Max. ECG no. on circuit breaker 10 A (B)	17 <sup>2)</sup>
Max. ECG no. on circuit breaker 16 A (B)	28 <sup>2)</sup>
Operating frequency	40...50 kHz

1) Minimum voltage for lamp ignition: 198 V, 185...198 V for maximum 1 h

2) Type B

### Light technical data

Starting time	2 s
---------------	-----

### Dimensions & Weight

Length	280.00 mm
Mounting hole spacing, length	270,0 mm
Width	30.00 mm
Height	28.00 mm
Cable cross-section, input side	0.5...1.5 mm <sup>2</sup> <sup>1)</sup>
Cable cross-section, output side	0.5...1.5 mm <sup>2</sup> <sup>1)</sup>
Product weight	179.5 g

1) Solid leads

### Colors & materials

Casing material	Metal
Body material	Metal

### Temperatures & operating conditions

Ambient temperature range	-15...+50 °C
Maximum temperature at tc test point	70 °C

Max.housing temperature in case of fault	110 °C
Permitted rel. humidity during operation	5...85 % <sup>1)</sup>

<sup>1)</sup> Maximum 56 days/year at 85 %

### Lifespan

ECG lifetime	50000 h <sup>1)</sup>
--------------	-----------------------

<sup>1)</sup> At maximum  $T_c$  / 10% failure rate

### Capabilities

Dimmable	No
Max. cable length to lamp/LED module	2.0 m / 1.0 m
Suitable for fixtures with prot. class	I
End of lamp life safety shutdown	EOL T.2





### Certificates & Standards





Approval marks – approval	VDE / VDE-EMC / ENEC 10 / CE
Standards	Acc. to EN 61347-2-3 / Acc. to EN 60929 / Acc. to EN 55015:2006 + A1:2007 / Acc. to EN 61000-3-2 / Acc. to EN 61547
Protection class	I
Type of protection	IP20
Energy efficiency class	A2
EEI – Energy Label	A2


### LOGISTICAL DATA

Temperature range at storage	-40...+85 °C
------------------------------	--------------

### DOWNLOAD DATA

	Documents and certificates	Document name
	User Instruction	590720_EAC QT-FIT8
	Declarations of conformity	339525_Declaration of Conformity (GB)
	Certificates	554891_EAC PT family
	Certificates	334974_ENEC-Marks approval

Documents and certificates		Document name
	Certificates	335097_INOTEC
	Certificates	335169_Manufacturer's declaration – Lamp/ECG combinations: Frequent switching
	Certificates	335150_CEAG
	Certificates	504209_VDE-EMC-Certificate QT-Fit8

CAD/BIM files		Document name
	CAD data 3D PDF	316099_QUICKTRONIC fit T8 QT-FIT8 280x30x28 9900049

**LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4008321294180	Unpacked 1		179.50 g	
4008321294197	Shipping box 20	311 mm x 131 mm x 161 mm	3759.00 g	6.56 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

**DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.